



WAFER(180°)

Part No: 3961S  
 Material: pin/post Brass Tin  
 Wafer: Nylon UL94V-2

Insulation resistance: 1000M OHM/min  
 Withstand voltage: 1500V AC/minute  
 Current rating: 5A AC/DC  
 Voltage rating: 250V AC/DC

Poles	Part NO.	Dimension (mm)	
		A	B
2	3961S-2P	3.96	7.92
3	3961S-3P	7.92	11.88
4	3961S-4P	11.88	15.84
5	3961S-5P	15.84	19.80
6	3961S-6P	19.80	23.76
7	3961S-7P	23.76	27.72
8	3961S-8P	27.72	31.68
9	3961S-9P	31.68	35.64
10	3961S-10P	35.64	39.60
11	3961S-11P	39.60	43.56
12	3961S-12P	43.56	47.52
13	3961S-13P	47.52	51.48
14	3961S-14P	51.48	55.44
15	3961S-15P	55.44	59.40
16	3961S-16P	59.40	63.36
17	3961S-17P	63.36	67.32
18	3961S-18P	67.32	71.28
19	3961S-19P	71.28	75.24
20	3961S-20P	75.24	79.20

TOLERANCE TABLE

.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD
CHECKED:	DATE:	
DRAWN:	DATE:	TITLE:
L.Y.F	2008-07-07	3961S-XP
CLIENT P/N		SCALE
UNIT	mm	free
FILE NO.	Ckmtw-3961-00012	REV. A
		WDD00