

# 559/560 Series Fuse Holders for TE5/TR5 Type Fuses










#### **Agency Approvals**


Agency	Agency File Number		
	559 Series	560 Series	
DYE	N/A	40041024	
<b>71</b>	N/A	E14721	

### **Dimensions** units in mm

## 559 Series



### 560 Series



Product Characteristics				
	559 Series (Lead Free)	560 Series		
Compatible Fuses	TR5/TE5	TR5/TE5		
Materials	<b>Holder:</b> Black Thermoplastic, UL94 V-0	<b>Holder:</b> Thermoplastic, UL 94 V-0		
	Metal Parts: Copper alloy; solderable tinned			
Electrical Data (23°C)	Rated Voltage: 250V			
	Max. Current/Power: 6.3 A /1.6 W			
Mounting	PC Board, 7.18 mm pin spacing	PC Board, 5.08 mm pin spacing		
Solderability	max. 260 °C, 10 s (Wave)			
Minimum Cross Section	Conducting path - 0.1 mm <sup>2</sup>			
Unit Weight	0.63 g	0,4 g		

Note: Ensure proper fuseholder re-rating.

## **Ordering Information**

Ordering Number	"A" Height Options	Packaging
559 0000 00 01	6.5 mm (code 0001)	1000 Pcs Bulk
559 0000 80 11	10 mm (code 8011)	100 Pcs Bulk
560 0000 13 19	3.0 mm (code 1319)	500 Pcs Bulk
560 0000 10 09	4.3 mm (code 1009)	500 Pcs Bulk
560 0000 10 19	4.3 mm (code 1019)	1000 Pcs Bulk

## **Additional Information**



Datasheet 559 Series



**Datasheet** 560 Series



Resources 559 Series



Resources 560 Series



Samples 559 Series



Samples 560 Series