



成都亿佰特电子科技有限公司

Chengdu Ebyte Electronic Technology Co.,Ltd.

TX433-JK-20 Datasheet v1.0

Picture

TX433-JK-20



Physical parameter

TX433-JK-20

No.	Parameter item	Parameter details & Description
1	Model	TX433-JK-20
2	Size	Ø 13.0 * 210 mm
3	Average Weight	20 ± 1 g
4	Shape Feature	Flexible
5	Color	Black
6	Material	TPEE
7	Connector Type	SMA-J
8	Cable Length	-

Electrical parameter

TX433-JK-20

No.	Parameter item	Parameter details & Description
1	Frequency Range	410 ~ 450 MHz
2	Gain	3 dBi
3	SWR	≤ 1.5
4	Power Capacity	10 W
5	Input Impedance	50 Ω
6	Polarization Type	Vertical polarization
7	Radiation Direction	Omnidirectional

Dimension **TX433-JK-20**




Test report **TX433-JK-20**

【Testing Instrument】 : Agilent E5071C


【Test address】 : Chengdu Ebyte Electronic Technology Co.,Ltd.

【Current Temperature】 : 26°C

【Title】 : Standing-wave ratio (SWR) test report by Agilent E5071C



【Title】 : Smith chart by Agilent E5071C



About us

TX433-JK-20



Chengdu Ebyte Electronic Technology Co., Ltd is a high-tech company, focus on wireless transmission. Our company owns a number of independent research & development products and obtain unanimously approved customers. With powerful R&D team, our company can provide customers with perfect After-sales service and technical assistance.



成都亿佰特电子科技有限公司
Chengdu Ebyte Electronic Technology Co.,Ltd.

【Website】 : www.cdebyte.com

【Technical Support】 : support@cdebyte.com

【eBay】 : stores.ebay.com/cdebyte

【Alibaba】 : cdebyte.en.alibaba.com

【Address】 : Innovation Center D347,4# XI-XIN road, High-tech district(West),Chengdu, Sichuan, China