


NOTE:
 Rating: DC 30V 0.1A
 Operating Force: 40±10gf
 Lifetime: 100,000 Cycles



PART NO.	H
K5-1130DA-01	8.5
K5-1130DA-02	11.0
K5-1130DA-03	12.3
K5-1130DA-04	13.7

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Contact Spring	—	1	Phosphor Bronze	Ag Plated	—
④	Terminal	—	4	Phosphor Bronze	Ag Plated	—
③	Base	—	1	NYLON	Black	—
②	Cover	—	1	NYLON	Black	—
①	Knob	—	1	NYLON	Black	—

APPROVALS		DATE
DRAWN	J.X.Zhong	2013/9/10

APPROVALS		TITLE:	PART NO.	SCALE:	PROJ:
CHECKED		DETECTOR SWITCHS	K5-1130DA-□□	1:1	④
APPROVALS					⑤
TOLERANCES ARE	30~12.5 ±0.30 10~30 ±0.20 5~10 ±0.15 ~5 ±0.10	ANGLE	UNIT: mm	DRAWING NO.	SHEET 1 OF 1

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			