

乐清博穆电子有限公司

产品规格书

编 号

PB141



版 本 号

19

产品名称

PHB 线对板连接器

产品编号



材
质: PA66

物料名称	物料号	A	B	C	物料名称	物料号	A	B	C
PHB- (2×2)AW		\	\	\	PHB- (2×11)AW		23.95	19.0	20.0
PHB- (2×3)AW		\	\	\	PHB- (2×12)AW		25.95	21.0	22.0
PHB- (2×4)AW		9.95	5.0	6.0	PHB- (2×13)AW		27.95	23.0	24.0
PHB- (2×5)AW		11.95	7.0	8.0	PHB- (2×14)AW		29.95	25.0	26.0
PHB- (2×6)AW		13.95	9.0	10.0	PHB- (2×15)AW		31.95	27.0	28.0
PHB- (2×7)AW		15.95	11.0	12.0	PHB- (2×16)AW		33.95	29.0	30.0
PHB- (2×8)AW		17.95	13.0	14.0	PHB- (2×17)AW		35.95	31.0	32.0
PHB- (2×9)AW		19.95	15.0	16.0	PHB- (2×18)AW		37.95	33.0	34.0
PHB- (2×10)AW		21.95	17.0	18.0	PHB- (2×19)AW		39.95	35.0	36.0
\		\	\	\	PHB- (2×20)AW		41.95	37.0	38.0

制 订

审 核

批 准