



PCB Layout (Pattern Side)

NO.1	
PART NO	H
A	3.15
C	3.85

NO.2	
PART NO	VIGOR
1	90±30
2	130±30
3	180±30
4	250±30
5	350±50

NO.3	
PART NO	MATERIAL/QTY
S	SUS/1PC
D	SUS/2PCS

NO.4-NO.5	
PART NO	NOTE
01~99	SERIAL NUMBER



ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Terminal	—	2	Brass(0.30t)	Plating silver	—
④	Contact	—	1	F.Ag/SUS	Plating silver	—
③	Base	—	1	PA66	Black	—
②	Cover	—	1	SPCC	Plating Nickel	—
①	Keystoke	—	1	PA66	White	—

APPROVALS		DATE	HRO 韓泰 ELECTRONICS CO.,LTD		
DRAWN	J.X.Zhang	2013/5/30	TITLE:	TACT SWITCHS	
CHECKED			PART NO.	K2-1101AT-□□□□-□□	
APPROVALS			TOLERANCES ARE	ANGLE	UNIT: mm SCALE: 1:1 PROJ:
			30~以下: ±0.30	±2'	DRAWING NO.
			10~30: ±0.20		SHEET 1 OF 1
			5~10: ±0.15		
			~ 5: ±0.10		

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			