



P.C.B LAYOUT(copper-sided view)



Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3-20N
 Operating Life:5,000cycles



② Terminal	3	Phosphor bronze	Au Plating
① Housing	1	Nylon	Black
ITEM	PART NAME	TER.NO.	QTY.
APPROVALS		DATE	
DRAWN	J.X.Zhang	2013/11/11	
CHECKED			
APPROVALS		TITLE:	PHONE JACKES
		PART NO.	DC-080
TOLERANCES ARE		UNIT:	mm
30~0.15	±0.30	SCALE:	1:1
10~0.30	±0.20	DRAWING NO.	
5~0.10	±0.15	PROJ.	
~5	±0.10	SHEET	1 OF 1
ECN NO.	REV.	DATE.	DESCRIPTION.
	A		NEW

