


P/N	DC-038/A-A	DC-038/A-B
Schematic code		



Rating:0.5A 30V DC  
 Contact Resistance:100 mΩ Max.  
 Operating temperature:-20℃~70℃  
 Operating force:3-20N  
 Operating Life:5,000cycles

② Terminal	3	Phosphor bronze	Au Plating			
① Housing	1	Nylon	Black			
ITEM	PART NAME	TER.NO.	QTY.	MATERIAL	FINISHING	REMARK
APPROVALS						
DRAWN	J.X.Zhang	DATE	2013/11/11	ELECTRONICS CO.,LTD		
CHECKED		TITLE:		PHONE JACKES		
APPROVALS		PART NO.	DC-038			

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			
TOLERANCES ARE						
	30~øL	±0.30	ANGLE			
	10~30	±0.20	UNIT: mm	SCALE: 1:1	PROJ.	
	5~10	±0.15	DRAWING NO.			
	~5	±0.10				SHEET 1 OF 1