



P.C.B LAYOUT(Copper-side view)



Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3-20N
 Operating Life:5,000cycles

② Terminal	4	Phosphor bronze	Au Plating
① Housing	1	Nylon	Black
ITEM	PART NAME	TERN.O.	QTY.
APPROVALS		DATE	
DRAWN	J.X.Zhang	2013/11/11	
CHECKED			
APPROVALS		TITLE:	DC JACKES
TOLERANCES ARE		PART NO.	DC-031A
30~12.5	±0.30	ANGLE	
10~30	±0.20	UNIT: mm	SCALE: 1:1
5~10	±0.15	DRAWING NO.	PROJ:
~5	±0.10		SHEET 1 OF 1
ECN NO.	REV.	DATE.	DESCRIPTION.
B			NEW
A			



ELECTRONICS CO.,LTD