



P.C.B LAYOUT(top view)



Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3-20N
 Operating Life:5,000cycles



Model No.	1	2	3
PIN	ø2.0	ø2.35	ø2.5

② Terminal	—	3	Phosphor bronze	Au Plating		
① Housing	—	1	Nylon	Black		
ITEM	PART NAME	TER.NO.	QTY.	MATERIAL	FINISHING	REMARK
APPROVALS		DATE	ELECTRONICS CO.,LTD			
DRAWN	J.X.Zhang	2013/11/11	PHONE JACKES			
CHECKED			DC-017			
APPROVALS			PART NO.			

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	TOLERANCES ARE	30±0.15	±0.30	ANGLE	PART NO.	SCALE:	PROJ.
	A		NEW				10±0.20	±0.20			DC-017	1:1	1 OF 1
							5±0.10	±0.15	±2'				
							~ 5	±0.10					SHEET