



DC MATE PLUG

P.C.B LAYOUT(top view)



Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3-20N
 Operating Life:5,000cycles



Model No.	1	2	3
PIN	ø2.0	ø2.35	ø2.5

② Terminal	3	Phosphor bronze	Au Plating
① Housing	1	Nylon	Black
ITEM	PART NAME	TER.NO.	QTY.
APPROVALS		DATE	
DRAWN	J.X.Zhang	2013/11/11	
CHECKED			
APPROVALS		TITLE:	PHONE JACKES
APPROVALS		PART NO.	DC-016
TOLERANCES ARE		SCALE:	1:1
30~0.15	±0.30	ANGLE	
10~0.30	±0.20	UNIT:	mm
5~0.10	±0.15	DRAWING NO.	
~5	±0.10		



ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			