



Model No.	1	2
PIN	∅1.0	∅1.3

P.C.B LAYOUT(Copper-side view)



DC MATE PLUG

Rating:0.5A 30V DC  
 Contact Resistance:100 mΩ Max.  
 Operating temperature:-20℃~70℃  
 Operating force:3-20N  
 Operating Life:5,000cycles

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.																																																																																				
	A		NEW																																																																																							
<table border="1"> <tr> <td>②</td> <td>Terminal</td> <td>3</td> <td>Phosphor bronze</td> <td>Au Plating</td> <td></td> <td></td> </tr> <tr> <td>①</td> <td>Housing</td> <td>1</td> <td>Nylon</td> <td>Black</td> <td></td> <td></td> </tr> <tr> <td>ITEM</td> <td>PART NAME</td> <td>TER.NO.</td> <td>QTY.</td> <td>MATERIAL</td> <td>FINISHING</td> <td>REMARK</td> </tr> <tr> <td colspan="4">APPROVALS</td> <td>DATE</td> <td colspan="2"></td> </tr> <tr> <td>DRAWN</td> <td>J.X.Zhang</td> <td colspan="2">2013/11/11</td> <td colspan="3">TITLE: PHONE JACKES</td> </tr> <tr> <td colspan="4">CHECKED</td> <td colspan="3">PART NO. DC-006</td> </tr> <tr> <td colspan="4">APPROVALS</td> <td colspan="3">DRAWING NO.</td> </tr> <tr> <td colspan="4">TOLERANCES ARE</td> <td>30~0.15</td> <td>±0.30</td> <td>ANGLE</td> </tr> <tr> <td colspan="4"></td> <td>10~0.30</td> <td>±0.20</td> <td>UNIT: mm</td> </tr> <tr> <td colspan="4"></td> <td>5~0.10</td> <td>±0.15</td> <td>SCALE: 1:1</td> </tr> <tr> <td colspan="4"></td> <td>~ 5</td> <td>±0.10</td> <td>PROJ. </td> </tr> <tr> <td colspan="4"></td> <td></td> <td></td> <td>SHEET 1 OF 1</td> </tr> </table>							②	Terminal	3	Phosphor bronze	Au Plating			①	Housing	1	Nylon	Black			ITEM	PART NAME	TER.NO.	QTY.	MATERIAL	FINISHING	REMARK	APPROVALS				DATE			DRAWN	J.X.Zhang	2013/11/11		TITLE: PHONE JACKES			CHECKED				PART NO. DC-006			APPROVALS				DRAWING NO.			TOLERANCES ARE				30~0.15	±0.30	ANGLE					10~0.30	±0.20	UNIT: mm					5~0.10	±0.15	SCALE: 1:1					~ 5	±0.10	PROJ.							SHEET 1 OF 1
②	Terminal	3	Phosphor bronze	Au Plating																																																																																						
①	Housing	1	Nylon	Black																																																																																						
ITEM	PART NAME	TER.NO.	QTY.	MATERIAL	FINISHING	REMARK																																																																																				
APPROVALS				DATE																																																																																						
DRAWN	J.X.Zhang	2013/11/11		TITLE: PHONE JACKES																																																																																						
CHECKED				PART NO. DC-006																																																																																						
APPROVALS				DRAWING NO.																																																																																						
TOLERANCES ARE				30~0.15	±0.30	ANGLE																																																																																				
				10~0.30	±0.20	UNIT: mm																																																																																				
				5~0.10	±0.15	SCALE: 1:1																																																																																				
				~ 5	±0.10	PROJ.																																																																																				
						SHEET 1 OF 1																																																																																				
 ELECTRONICS CO.,LTD																																																																																										