


Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3-20N
 Operating Life:5,000cycles



ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

DRAWN	J.X.Zhang	DATE	2013/11/11
CHECKED		TITLE	PHONE JACKES
APPROVALS		PART NO.	DC-005B
TOLERANCES ARE			
30~0.15	±0.30	ANGLE	
10~0.30	±0.20	UNIT: mm	SCALE: 1:1
5~0.10	±0.15	DRAWING NO.	
~5	±0.10		PROJ. SHEET 1 OF 1

②	Terminal	3	Phosphor bronze	Au Plating		
①	Housing	1	Nylon	Black		
ITEM	PART NAME	TER.NO.	QTY.	MATERIAL	FINISHING	REMARK
APPROVALS						
DRAWN J.X.Zhang DATE 2013/11/11						
TITLE: PHONE JACKES						
PART NO. DC-005B						
ELECTRONICS CO.,LTD						