



NOTE:
 Rating: DC 30V 0.1A
 Operating Force: 20 ± 10 gf
 Lifetime: 50,000 Cycles

PCB Layout (Pattern side)

⑤	Contact Spring	—	1	Be Alloy	Ag Plated	—
④	Terminal	—	2	Phosphor Bronze	Ag Plated	—
③	Cover	—	1	SUS	Natural	—
②	Housing	—	1	LCP	Black	—
①	Slider	—	1	PA46	Black	—

APPROVALS		DATE	TITLE: DETECTOR SWITCHES	
DRAWN J.X.Zhang		2013/8/26	ELECTRONICS CO.,LTD	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			
TOLERANCES ARE						
		30~0.12	± 0.30	ANGLE		PART NO. K5-1617SA-01
		10~30	± 0.20	UNIT: mm		SCALE: 1:1
		5~10	± 0.15	DRAWING NO.		PROJ. SHEET 1 OF 1
		~5	± 0.10			