




Circuit Diagram



PCB Layout(Pattern side)

NOTE:  
 Rating: DC 20V 50mA  
 Operating Force: 20±10gf  
 Lifetime: 100,000 Cycles

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Spring	—	1	SUS	Ag Plated	—
④	Terminal	—	4	Phosphor Bronze	Ag Plated	—
③	Cover	—	1	PA46	Black	—
②	Base	—	1	PA46	Black	—
①	Slider	—	1	PA46	Black	—

APPROVALS		DATE	TITLE:	
DRAWN	J.X.Zhang	2013/9/22	ELECTRONICS CO.,LTD	
CHECKED			DETECTOR SWITCHS	
APPROVALS			PART NO.	K5-1616SA-01

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	TOLERANCES ARE	ANGLE	UNIT:	SCALE:	PROJ.	SHEET
	A		NEW				30~0.15 10~0.30 5~1.0	±0.30 ±0.20 ±0.15	mm	1:1	PROJ. 1 OF 1	1 OF 1