


Circuit Diagram

PCB Layout (Pattern side)



| PART NO. | L | Operating force |
|-------------|---|-----------------|
| K3-2235S-F□ | 2 | 200±100gf |
| K3-2235S-K□ | 3 | |
| K3-2235S-L□ | 4 | |

□:KNOB 1:Black 2:White

| ITEM | PART NAME | TER'NO. | QTY. | MATERIAL | FINISHING | REMARK |
|------|----------------|---------|------|------------------|-----------|--------|
| ⑤ | Contact Spring | — | 2 | Beryllium copper | Ag Plated | — |
| ④ | Terminal | — | 6 | Brass Strip | Ag Plated | — |
| ③ | Base | — | 1 | NYLON | Black | — |
| ② | Cover | — | 1 | SUS | Natural | — |
| ① | KNOB | — | 1 | NYLON | White | — |

| APPROVALS | | DATE |
|-----------|------------|------------|
| DRAWN | xu qi feng | 2014.11.03 |



ELECTRONICS CO.,LTD

| CHECKED | TITLE: | TOGGLE SWITCHES |
|-----------|----------|-----------------|
| APPROVALS | PART NO. | |

| ECN NO. | REV. | DATE. | DESCRIPTION. | CHANGE. | CHECK. | APPRO. |
|---------|------|-------|--------------|---------|--------|--------|
| | A | | NEW | | | |

| TOLERANCES ARE | 30~125μm | ±0.30 | ANGLE | UNIT: | SCALE: | PROJ: |
|----------------|----------|-------|-------|-------------|--------|--------------|
| 10~30 | ±0.20 | | ° | mm | 1:1 | ① |
| 5~10 | ±0.15 | | | | | |
| ~5 | ±0.10 | | ±2' | DRAWING NO. | | SHEET 1 OF 1 |