


NTC Thermistors, Mini Lug Sensors



QUICK REFERENCE DATA		
PARAMETER	VALUE	UNIT
Resistance value at 25 °C	10K to 47K	Ω
Tolerance on R_{25} -value	± 2 to ± 3	%
$B_{25/85}$ -value	3740 to 3984	K
Tolerance on $B_{25/85}$ -value	± 0.5 to ± 1.5	%
Operating temperature range: At zero dissipation	-40 to +125	°C
Response time	3.5	s
Thermal time constant τ	≈ 5	s
Dissipation factor δ	10	mW/K
Min. dielectric withstanding voltage between terminals and lug	1000	V _{AC}
Climatic category (LCT / UCT / days)	40 / 125 / 56	-
Weight		
without connector	~ 0.5	g
with connector	~ 0.6	g

Note

- Other R_{25} values and tolerances available upon request

FEATURES

- Fast time response for surface applications compared to industry standard NTC lug sensors
- Reduced thermal gradient, due to the use of small dimensions and nickel conductor, allowing for an accurate surface temperature measurement
- The sensor is not suitable for being permanently in contact with water or liquids
- Small size connector and small lug ring tongue terminal, allowing for temperature sensing at locations where only limited space is available
- Mounting: assembly screw mounting
- Connector ZHR-2 (optional)
- AEC-Q200 qualified available (grade 1)
- UL recognized, file E148885 (UL category XGPU2)
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS COMPLIANT

APPLICATIONS

Thermistors used for surface temperature sensing and control in:

- Computer equipment
- MOSFETS, IC's, Power Electronics, heatsink temperature control, LED emitter heat-sink control
- Consumer appliances
- Industrial equipment
- Automotive equipment

DESCRIPTION

Miniature insulated chip thermistor with a negative temperature coefficient mounted inside a mini lug barrel. The device has no marking.

MOUNTING

- The sensor can be mounted by means of a screw. For stud size, metric 2 mm M2/American stud #1-2
- The end wire can be soldered, welded or crimped to a connector
- Optional connector for Wire-to-Wire or Wire-to-Board connections


ELECTRICAL DATA AND ORDERING INFORMATION						
R_{25} (Ω)	R_{25} -TOL. (± %)	$B_{25/85}$ (K)	$B_{25/85}$ -TOL. (± %)	DESCRIPTION	UL RECOGNIZED (Y / N)	SAP MATERIAL AND ORDERING NUMBER
10 000	2	3984	0.5	NTC Mini Lug 10K 2 % 3984 K 0.5 %	Y	NTCALUG03A103G
10 000	2	3984	0.5	NTC Mini Lug 10K 2 % 3984 K 0.5 % with connector	Y	NTCALUG03A103GC
10 000	3	3984	0.5	NTC Mini Lug 10K 3 % 3984 K 0.5 %	Y	NTCALUG03A103H
10 000	3	3984	0.5	NTC Mini Lug 10K 3 % 3984 K 0.5 % with connector	Y	NTCALUG03A103HC
12 000	3	3740	1.5	NTC Mini Lug 12K 3 %	N	NTCALUG03A123H
12 000	3	3740	1.5	NTC Mini Lug 12K 3 % with connector	N	NTCALUG03A123HC
47 000	3	3740	1.5	NTC Mini Lug 47K 3 %	N	NTCALUG03A473H
47 000	3	3740	1.5	NTC Mini Lug 47 kΩ 3 % with connector	N	NTCALUG03A473HC

Note

- Ordering information can be found on: www.vishay.com/doc?33036



DIMENSIONS in millimeters



L ₁	L ₂	L ₃	L ₄	L ₁ + L ₃ (item without connector)	Ø D ₁	Ø D ₂	Ø D ₃	Ø D ₄	T	Pitch P
70 ± 5	4 ± 1	11.5 ± 0.3	8.8 ± 0.3	81.5 ± 5	2.2 ± 0.3	5.5 ± 0.3	3.4 ± 0.3	0.35 ± 0.1	0.8 ± 0.1	1.5 ± 0.3

Notes

- (1) Vishay Thermistor chip NTC, with epoxy coating and middle buffer layer
- (2) Metal ring lug, tin plated
- (3) Insulated leads: AWG#32, monostranded, diam 0.20 mm, silver plated Nickel, ETFE insulated, diameter 0.35 mm
- (4) End wire stripped or 2-poles connector crimped (optional)

MOUNTING

- With screw size metric M2, or American stud 1-2
- For the type without connector, the electrical connection can be made by soldering, crimping or welding.
- For the type with connector, the connector can mate with following counter-connectors ⁽⁵⁾:
 - A. One of the PCB connector - Through Hole:
 - JST B 2B-ZR (top entry)
 - JST S 2B-ZR (side entry)
 - JST B 2B-ZR-3.4 (top entry, for 1.6 mm board)
 - JST S 2B-ZR-3.4 (side entry, for 1.6 mm board)
 - B. One of the PCB Board connector - SMT Surface Mount:
 - JST S 2B-ZR-SM2-TF (SM2 side entry)
 - JST B 2B-ZR-SM3-TF (SM3 top entry)
 - JST S 2B-ZR-SM3A-TF (SM3 side entry)
 - JST B 2B-ZR-SM4-TF (SM4 top entry)
 - JST S 2B-ZR-SM4A-TF (SM4 side entry)
 - C. The Wire-to-wire connector:
 - JST ZMR-02 housing (x 1) + JST SMM-003T-P0.5 terminals (x 2)

Note

⁽⁵⁾ Additional details and dimensions can be found in JST ZH and JST ZM datasheets.

PACKAGING

Available in plastic bags of 250 pieces. SPQ = 2000 pieces

DESIGN-IN SUPPORT

- Other resistance curves and tolerances are available on request
- Consult Vishay for other lead length, other connector crimping or other features
- Other applicable screw size are available, for example M3 (American Stud #3-4)
- 3D solid models: www.vishay.com/doc?29106
- NTC curve computation: www.vishay.com/thermistors/ntc-curve-list/
- For M3 (American Stud #3/4) size, series NTCALUG39 is available for limited R₂₅ values.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.