





NOTE:

1. ALL DIMENSIONS ARE IN MILLIMETERS,
2. GENERAL TOLERANCES MAX. ±0.20mm.

BRACKETED DIMENSIONS

ARE IN INCHES.



DTSM-62~66□-V	0.6 MAX	.0236MAX
DTSM-61□-V	0.5 MAX	.0197MAX
PROD. NO.	1	INCHES.

DTSM-66□-V	13.0[.512]
DTSM-65□-V	9.5[.374]
DTSM-63□-V	7.0[.275]
DTSM-62□-V	5.0[.197]
DTSM-61□-V	4.3[.169]
PROD. NO.	H

APPD:	QTY:	SCALE:	8 : 1	REV:	A	PART NO.:	FINISH:	PART NAME:	7ACTILE SWITCH SMT TYPE
CHKD:	DR:	DESIGN:	MM	DATE:	03.16.09	APPD.		DIPTRONICS MANUFACTURING INC.	030
ZONE/REV:	A	DESCRIPTION:						DWG NO.:	R D 5 P 6 M - V