

● ELECTRICAL PARAMETERS

谐振器产品技术指标	Min	Max	Units
1. Holder Type(型号规格)	SEAM 3.2*2.5		
2. Mode of Oscillation (振动模式)	FUND		
3. Frequency (标称频率)	12.000000		MHz
4. Load Capacitance (CL) (负载电容)	10 ±10%		pF
5. Shunt Capacitance (Co) (静态电容)	0	7	pF
6. Equivalent Resistance (谐振电阻)		80	Ω
7. Frequency Tolerance at 25°C (调整频差)	-10	10	ppm
8. Stability over operation temperature (温度频差)	± 50		ppm
9. Insulation Resistance (at DC 100V) (绝缘电阻)	500		MΩ
10. Drive Level (激励功率)	10		uw
11. Operating Temperature Range (工作温度范围)	-40	85	°C
12. Storage Temperature Range (储存温度范围)	-40	125	°C
13. Aging (老化率)	± 5		ppm/year
14. Other(其他)	DLD2<10 FDL D<10(0.01-100/STEP10)		

OUTLINE DIMENSIONS(UNIT:mm) 外形尺寸 (单位: mm)

