



Specification

Current Rating : 1A
 Contact Resistance : 20mΩ Max
 Insulation Resistance : 1000MΩ Min.at 500V DC
 Dielectric Withstanding Voltage : 500V AC for 1 Minute
 Operation Temperature : -55 ° C ~ +105 ° C

Material

Insulator : P.B.T+30%Glass Fiber(UL94V-0)
 Contact : Phosphor Bronze or Brass
 Contact Plated : 0.8u" Gold over Nickel or Tin

POLES	PART No.	Dim. A	Dim. B	Dim. C
6	101-6P	12.19	5.08	6.35
8	101-8P	14.73	7.62	8.89
10	101-10P	17.27	10.16	11.43
12	101-12P	19.81	12.70	13.97
14	101-14P	22.35	15.24	16.51
16	101-16P	24.89	17.78	19.05
20	101-20P	29.97	22.86	24.13
24	101-24P	35.05	27.94	29.21
26	101-26P	37.59	30.48	31.75

POLES	PART No.	Dim. A	Dim. B	Dim. C
30	101-30P	42.67	35.56	36.83
34	101-34P	47.75	40.64	41.91
40	101-40P	55.37	48.26	49.53
44	101-44P	60.45	53.34	54.61
50	101-50P	68.07	60.96	62.23
56	101-56P	75.69	68.58	69.85
60	101-60P	80.77	73.66	74.93
62	101-62P	83.31	76.20	77.47
64	101-64P	85.85	78.74	80.01

TOLERANCE TABLE	
.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	深圳市矽科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD
CHECKED:	DATE:	
DRAWN:	DATE:	TITLE:
L.Y.F	2008-04-07	101-XP 三件式 有凸
CLIENT P/N		UNIT
/		mm
SCALE		free
FILE NO.		REV.
Ckmtw-101-0001		A