



SPECIFICATIONS

Current rating: 3A AC/DC
 Voltage rating: 250V AC/DC
 Contact resistance: 20mΩ max.
 Withstand voltage: 1000V AC/min
 Insulation resistance: 1000MΩ/min.
 Temperature range: -25°C~+85°C
 Applicable PC board thickness: 0.063"(1.6)

Material:
 Part No: 2~20
 Post: Brass, Tin/plated
 Base: Nylon66 UL94V-2

Poles	Part No.	Dimension mm	
		A	B
2	2501SB-2P	2.50	7.50
3	2501SB-3P	5.00	10.00
4	2501SB-4P	7.50	12.50
5	2501SB-5P	10.00	15.00
6	2501SB-6P	12.50	17.50
7	2501SB-7P	15.00	20.00
8	2501SB-8P	17.50	22.50
9	2501SB-9P	20.00	25.00
10	2501SB-10P	22.50	27.50
11	2501SB-11P	25.00	30.00
12	2501SB-12P	27.50	32.50
13	2501SB-13P	30.00	35.00
14	2501SB-14P	32.50	37.50
15	2501SB-15P	35.00	40.00
16	2501SB-16P	37.50	42.50
17	2501SB-17P	40.00	45.00
18	2501SB-18P	42.50	47.50
19	2501SB-19P	45.00	50.00
20	2501SB-20P	47.50	52.50

TOLERANCE TABLE	
.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	TITLE: 2501SB-XP 带扣			
CHECKED:	DATE:	CLIENT P/N /			
DRAM: LYF	DATE: 2008-04-07	UNIT: mm	SCALE: Free	REV. A	KL00
		FILE NO. Chantw-2501-0007			

深圳市灿科盟实业有限公司
 CHANKLEMENT INDUSTRY CO., LTD