



SPECIFICATIONS
 Current rating: 3A AC/DC
 Voltage rating: 250V AC/DC
 Contact resistance: 20mΩ max.
 Withstand voltage: 1000V AC/min
 Insulation resistance: 1000MΩ/min
 Temperature range: -25°C~+85°C
 Applicable PC board thickness: 0.063"(1.6)

Material:
 Part No: 2~20
 Housing: Nylon66, UL 94V-0



Poles	Part No.	Dimension mm	
		A	B
2	2501H-2P	2.50	7.60
3	2501H-3P	5.00	10.10
4	2501H-4P	7.50	12.60
5	2501H-5P	10.00	14.10
6	2501H-6P	12.50	17.60
7	2501H-7P	15.00	20.10
8	2501H-8P	17.50	22.60
9	2501H-9P	20.00	25.10
10	2501H-10P	22.50	27.60
11	2501H-11P	25.00	30.10
12	2501H-12P	27.50	32.60
13	2501H-13P	30.00	35.10
14	2501H-14P	32.50	37.60
15	2501H-15P	35.00	40.10
16	2501H-16P	37.50	42.60
17	2501H-17P	40.00	45.10
18	2501H-18P	42.50	47.60
19	2501H-19P	45.00	50.10
20	2501H-20P	47.50	52.60

APPROVED:	DATE:	TITLE: 2501H-XP			
CHECKED:	DATE:	CLIENT P/N /			
DRAMN:	DATE:	UNIT	SCALE	REV.	
LYF	2008-04-07	mm	Free	A	
TOLERANCE TABLE		FILE NO.	Chantw-2501-0001		
.0	±0.20	REVISION A			
.00	±0.10				
.000	±0.05				

深圳市矽科盟实业有限公司
 KENTW CHANKLEMENT INDUSTRYCO., LTD