



**WAFER(90°)**

**Part No:** 2510R  
**Wafer:** Nylon 66 UL94V-2  
**Material:** pin/post Brass tin plated  
**Circuits:** 2-20circuits available  
**Insulation resistance:** 1000M OHM/min  
**Withstand voltage:** 1000V AC/minute  
**Current rating:** 3A AC/DC  
**Voltage rating:** 250V AC  
**Temperature range:** -25°C to +85°C

Circuits	Part NO	Dimension(mm)	
		A	B
2	2510RF-2P	2.54	5.08
3	2510RF-3P	5.08	7.62
4	2510RF-4P	7.62	10.16
5	2510RF-5P	10.16	12.70
6	2510RF-6P	12.70	15.24
7	2510RF-7P	15.24	17.78
8	2510RF-8P	17.78	20.32
9	2510RF-9P	20.32	22.86
10	2510RF-10P	22.86	25.40
11	2510RF-11P	25.40	27.94
12	2510RF-12P	27.94	30.48
13	2510RF-13P	30.48	33.02
14	2510RF-14P	33.02	35.56
15	2510RF-15P	35.56	38.10
16	2510RF-16P	38.10	40.64
17	2510RF-17P	40.64	43.18
18	2510RF-18P	43.18	45.72
19	2510RF-19P	45.72	48.26
20	2510RF-20P	48.26	50.80

**TOLERANCE TABLE**

.0	±0.20
.00	±0.10
.000	±0.05

<b>APPROVED:</b>	<b>DATE:</b>	<b>TITLE:</b>			
<b>CHECKED:</b>	<b>DATE:</b>	2510RF-XP (贴片)			
<b>DRAMM:</b>	<b>DATE:</b>	<b>UNIT</b>	<b>SCALE</b>	<b>REV.</b>	<b>A</b>
LYP	2008-04-07	mm	Free		
		<b>FILE NO.</b>			
		Chartw-2510-0005			

深圳市灿科盟实业有限公司  
 CHARTW CHANKLEMENT INDUSTRYCO., LTD