



P.C.B LAYOUT

SPECIFICATIONS

Current rating: 2A AC/DC
 Voltage rating: 250V AC/DC
 Contact resistance: 20mΩ max.
 Withstand voltage: 800V AC/min
 Insulation resistance: 1000MΩ/min.
 Temperature range: -25°C~+85°C
 Applicable PC board thickness: 0.031"~0.063"(0.8~1.6)

Material:

Part No: 2~15
 Post: Brass, Tin plated
 Base: PA66, UL94V-2

Poles	Part No.	Dimension mm	
		A	B
2	2001R-2P	2.0	6.0
3	2001R-3P	4.0	8.0
4	2001R-4P	6.0	10.0
5	2001R-5P	8.0	12.0
6	2001R-6P	10.0	14.0
7	2001R-7P	12.0	16.0
8	2001R-8P	14.0	18.0
9	2001R-9P	16.0	20.0
10	2001R-10P	18.0	22.0
11	2001R-11P	20.0	24.0
12	2001R-12P	22.0	26.0
13	2001R-13P	24.0	28.0
14	2001R-14P	26.0	30.0
15	2001R-15P	28.0	32.0

TOLERANCE TABLE	
.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	TITLE:	CLIENT P/N	UNIT	SCALE	REV.
CHECKED:	DATE:	2001R-XP 贴弯 无定位	/	mm	free	⊕
DRAWN:	DATE:	深圳市灿科盟实业有限公司	FILE NO.	Chartw-2001-0006		∇
LYP	2008-05-28	Chantw CHANKLEMENT INDUSTRYCO., LTD				A