



Circuits	Part NO	Dimension (mm)	
		A	B
2	2510H-2P	5.6	2.54
3	2510H-3P	8.1	5.08
4	2510H-4P	10.7	7.62
5	2510H-5P	13.2	10.16
6	2510H-6P	15.8	12.70
7	2510H-7P	18.3	15.24
8	2510H-8P	20.8	17.78
9	2510H-9P	23.4	20.32
10	2510H-10P	25.9	22.86
11	2510H-11P	28.5	25.40
12	2510H-12P	31.0	27.94
13	2510H-13P	33.5	30.48
14	2510H-14P	36.1	33.02
15	2510H-15P	38.6	35.56
16	2510H-16P	41.2	38.10
17	2510H-17P	43.7	40.64
18	2510H-18P	46.2	43.18
19	2510H-19P	48.7	45.72
20	2510H-20P	51.3	48.26

SPECIFICATIONS

Current rating: 3A AC/DC
 Voltage rating: 250V AC/DC
 Contact resistance: 20mΩ max.
 Withstand voltage: 1000V AC/min
 Insulation resistance: 1000MΩ/min.
 Temperature range: -25°C~+85°C

Material:
 Part No: 2~20
 Housing: Nylon66, UL 94V-2

TOLERANCE TABLE

.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD
CHECKED:	DATE:	
DRAWN:	DATE:	TITLE:
LYF	2008-04-07	2510H-XP
CLIENT P/N		/
UNIT	mm	SCALE
FILE NO.	Ckmtw-2510-0001	free
REV.	A	free