



**WAFER(180°)**

Part No: 2~20  
 Wafer: Nylon 66 UL94V-2  
 Material: pin/post Brass tin plated  
 Circuits: 2-20circuits available  
 Insulation resistance: 1000M OHM/min  
 Withstand voltage: 1000V AC/minute  
 Current rating: 3A AC/DC  
 Voltage rating: 250V AC

Circuits	Part NO	Dimension (mm)	
		A	B
2	2510S-2P	2.54	5.08
3	2510S-3P	5.08	7.62
4	2510S-4P	7.62	10.16
5	2510S-5P	10.16	12.70
6	2510S-6P	12.70	15.24
7	2510S-7P	15.24	17.78
8	2510S-8P	17.78	20.32
9	2510S-9P	20.32	22.86
10	2510S-10P	22.86	25.40
11	2510S-11P	25.40	27.94
12	2510S-12P	27.94	30.48
13	2510S-13P	30.48	33.02
14	2510S-14P	33.02	35.56
15	2510S-15P	35.56	38.10
16	2510S-16P	38.10	40.64
17	2510S-17P	40.64	43.18
18	2510S-18P	43.18	45.72
19	2510S-19P	45.72	48.26
20	2510S-20P	48.26	50.82

TOLERANCE TABLE	
.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:
CHECKED:	DATE:
DRAWN:	DATE:
L.Y.F	2008-04-07

**Ckmtw** 深圳市灿科盟实业有限公司  
 CHANKLEMENT INDUSTRYCO., LTD

TITLE: 2510S-XP

CLIENT P/N	/
UNIT	mm
SCALE	free
FILE NO.	Ckmtw-2510-00003
REV.	A
WD00	