



P.C.B LAYOUT

**SPECIFICATION**

Poles: 2-24  
 Voltage rating: AC, DC 250V  
 Current rating: AC, DC, 7A  
 Withstand voltage: 1500V AC min.  
 Insulation resistance: 1000MΩ min.  
 Temperature range: -25℃ ~ +85℃  
 Applicable PC board thickness: 0.031" ~ 0.063"  
 (0.8 ~ 1.6mm)  
 Contact resistance: Initial value 10mΩ max.  
 After environmental testing 20mΩ max.  
 Material: Nylon66 UL94V-2

TOLERANCE TABLE	
.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	<b>Chantw</b> 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD
CHECKED:	DATE:	
DRAWN:	DATE:	TITLE:
LYP	2008-04-07	5557R-2*XP
CLIENT P/N		UNIT
/		mm
SCALE		free
FILE NO.	Chantw-5557-0011	REV.
		A