




RECOMMENDED P.C.B LAYOUT

TOLERANCE: ±0.05



MAPX	MODIFICATION	DATE
------	--------------	------

备注:

1. 材质:  
胶芯: PBT+30%G. F.  
端子: 青铜C2680, T=0.25mm.  
外壳: 青铜C2680/SPCC, T=0.30mm.
2. 电镀:  
端子: 镍底50u", 镀锡100u",  
接触区域按客户要求镀金.  
外壳: 镀可焊性镍80u"以上.
3. 电气性能:  
接触阻抗: 30 mΩ Max.  
绝缘电阻: 1000 MΩ Min.  
耐压: 500VAC/1分钟.  
额定电流: 1.5 A.
4. 机械性能:  
插入力: 3.57Kgf Max.  
拔出力: 1.02Kgf Min.
5. 其它:  
工作温度: -40° C 至 85° C.
6. 产品料号: 阅图fSimSun|b0|i0|c0|p2;:  
接触阻抗: 30 mΩ Max.  
绝缘电阻: 1000 MΩ Min.  
耐压: 500VAC/1分钟.  
额定电流: 1.5 A.

USAX-04FX-XNMX-D6

- 1-G.P
- 2-RoHS
- 3-REACH
- 4-HF/无卤
- 1-半光亮锡 1u"
- 2-半光亮锡 3u"
- 3-半光亮锡 5u"
- 4-半光亮锡 10u"
- 5-半光亮锡 15u"
- 6-半光亮锡 25u"
- 7-半光亮锡 30u"
- 1-卷带包装
- 2-PVC盒
- K-黑色
- W-白色
- N-本色

产品图 PRODUCT CHART DWG				深圳市精拓金电子有限公司						
公差一览表 TOLERANCE UNLESS OTHERWISE				单位 UNITS	MM	制图 DRAWING	Z-Y-B	制图料号 PRODUCT PART NO.		
X.	±0.25	X.	±5.°	比例 SCALE	1:1	审核 CHKD		产品名称 PRODUCT NO.	USB AF 短体反向插板成品 有卷边 加高8.70H(10.0L)	
.X	±0.20	.X	±2.°	日期 DATE	2013.09.24	核准 APPD		角法 VIEW	版本 VER	A0
.XX	±0.15	.XX	±1.°							
.XXX	±0.10	.XXX	±0.5°							