



RECOMMENDED P.C.B LAYOUT(±0.05)

- NOTE:
- MATERIAL:
 - INSULATOR: UL 94V-0
 - CONTACT: (T=0.20mm)
 - SHELL: (T=0.30mm)
 - ELECTRICAL CHARACTERISTICS:
 - CONTACT RESISTANCE: 30mΩ MAXIMUM
 - CONTACT CURRENT RATING: 1.5A
 - DIELECTRIC WITHSTANDING VOLTAGE: 500 V R.M.S.
 - MECHANICAL CHARACTERISTICS:
 - MATING FORCE: 3.57kg MAX
 - UNMATED FORCE: 1.02kg MIN
 - DURABILITY: MANDATORY: 1500 CYCLES
 - PLATING:
 - TERMINAL: 50u" MIN NICKEL ALL OVER
100u" MIN TIN ON SOLDER AREA
(1~30)u" Au ON CONTACT AREA
 - SHELL: 100u" MIN. NICKEL ALL OVER

5	SHELL	1	COPPER ALLOY	NI PLATED
4	SPIN	5	COPPER ALLOY	AU/TIN PLATED
3	4PIN	4	COPPER ALLOY	AU/TIN PLATED
2	COVER	1	THERMOPLASTIC	(UL 94V-0) BLUE
1	HOUSING	1	THERMOPLASTIC	(UL 94V-0) BLUE
No.	PART NAME	QTY	MATERIAL	REMARK

产品图

深圳市精拓金电子有限公司

公差一览表

单位: MM

公差	公差	公差	公差	公差	公差	公差	公差	公差	公差
X	±0.30	X	±5.°	日期	2016-12-05	制图	Gavin	制图料号	
.X	±0.25	.X	±2.°	比例	1:1	审核	郭治富	产品名称	USB 3.0 A/F 180° 有卷边H1.5
.XX	±0.15	.XX	±1.°	日期		核准	黄国荣	产品编号	
.XXX	±0.10	.XXX	±0.5°	日期		核准		角法	