




MAPX	MODIFICATION	DATE


NOTES:
1.ELECTRONIC:
CONTACT RESISTANCE: 30mohm MAX
INSULATION RESISTANCE: 1000 Mohm MIN
WITHSTAND VOLTAGE: AC 500V,1min.

2.MECHANICAL:
DURABILITY: 1500 CYCLE.
3.ENVIRONMENT CHARACTERISTICS:
OPERING TEMPERATURE:-55°C TO +105°C
4.RECOMMANDER PCB THICKNESS 1.2 TO 1.60MM

5	SHELL	1	COPPER ALLOY	NI PLATED
4	SPIN	5	COPPER ALLOY	AU/7IN PLATED
3	4PIN	4	COPPER ALLOY	AU/7IN PLATED
2	COVER	1	THERMOPLASTIC	(UL 94V-0) BLUE
1	HOUSING	1	THERMOPLASTIC	(UL 94V-0) BLUE
No.	PART NAME	QTY	MATERIAL	REMARK



RECOMMENDED P.C.B LAYOUT(±0.05)



产品图	制图	深圳市精拓金电子有限公司	
PRODUCT CHART DWG	DRAWING		

公差一览表		单位	MM	制图	制图料号
TOLERANCE UNLESS OTHERWISE		UNITS		DRAWING	PRODUCT NO.
X	±0.35	X	±5°	审核	产品名称
X	±0.30	X	±2°	CHD	PRODUCT NO.
XX	±0.20	XX	±1°	核准	角法
XXX	±0.10	XXX	±0.5°	DATE	VER
				2016-03-07	黄国荣
				APD	版本
					AO