



RECOMMENDED PCB LAYOUT (TOP VIEW)
GENERAL TOLERANCE +/-0.05

NOTES:
1. MATERIAL: HOUSING THERMOPLASTIC, UL 94V-0, COLOR: BLACK
CONTACT: COPPER ALLOY T=0.20mm
SHELL: STAINLESS STEEL T=0.40mm
SHELL: STAINLESS STEEL T=0.25mm
2. FINISH: CONTACT: 10µ MIN GOLD PLATING ON CONTACT AREA
G/F: PLATING ON SOLDER TAILS
SHELL: G/F PLATING ON SOLDER TAILS

Pin No.	SIGNAL
1	SCC1
2	DP1
3	DN1
4	PWR_IN_A
5	PWR_IN_B
6	DN2
7	DP2
8	ACC2
9	DETECT_1
10	DETECT_2
	SHELL_A GND
	SHELL_B GND

深圳市精拓金电子有限公司

UNLESS OTHERWISE SPECIFIED TOLERANCE		模貝編號		零件規格		圖紙名稱		產品圖	
尺寸公差範圍	角度公差範圍	單位	產品名稱	SMT 沉板 1.6 母座	零件編號	膠料			
X	X	MM	審核		零件材質	收縮			
.XX	.XX	1/1	承認		零件硬度	版次			
.XXX	.XXX	A3	製圖	夏雷	零件數量	頁次	1/1		