








REV	MARK	REVISIONS	SIGN	DATE
版本	记號	改動內容	修改	日期



RECOMMENDED PCB LAYOUT(TOP VIEW)
GENERAL TOLERANCE +/-0.05



NOTES:
1)MATERIAL:
HOUSING: THERMOPLASTICUL 94V-0,
COLOR: BLACK
CONTACT: COPPER ALLOY T=0.20mm
SHELL: STAINLESS STEEL T=0.40mm
SHELL: STAINLESS STEEL T=0.25mm
2)FINISH:
CONTACT: 6" MIN GOLD PLATING ON CONTACT AREA
G/F: PLATING ON SOLDER TABS
SHELL: G/F PLATING ON SOLDER TABS

Pin No.	SIGNAL
1	SCC1
2	DP1
3	DN1
4	PWR_IN_A
5	PWR_IN_B
6	DN2
7	DP2
8	ACC2
9	DETECT_1
10	DETECT_2
SHELL_A	GND
SHELL_B	GND

深圳市精拓金电子有限公司

UNLESS OTHERWISE SPECIFIED TOLERANCE		模貝編號		零件規格		圖紙名稱	
尺寸公差範圍	角度公差範圍	產品名稱	SMT 贴片母座	零件編號	產品圖	產品圖	
X, .XX, .XXX	X, .XX, .XXX	單位	MM	審核	製圖	膠料	收縮
		SCALE	1/1	承認	夏雷	零件材質	版次
		比例	1/1	製圖	夏雷	零件硬度	A
		尺寸	A3	製圖	夏雷	零件數量	頁次
							1/1