


Pin No.	SIGNAL
1	SCC1
2	DP1
3	DN1
4	PWR_IN_A
5	PWR_IN_B
6	DN2
7	DP2
8	ACC2
9	DETECT_1
10	DETECT_2
SHELL_A	GND
SHELL_B	GND

**SPECIFICATION**

**MATERIAL**  
See drawing

**STANDARD DATA**  
Operating temperature: -10°C ~ +60°C  
Storage temperature: -20°C ~ +85°C

**ELECTRICAL**  
Insulator resistance: 100Mohms Min.  
Withstanding voltage: 100 VAC / minute  
Contact resistance: Initial 40mohms Max;  
after 50mohms Max.



MAPX	MODIFICATION	DATE

# 深圳市精拓金电子有限公司

公差一览表		单位		制图		制图料号	
TOLERANCE UNLESS OTHERWISE	UNITS	MM	DRAWING	PRODUCT PART NO.	PRODUCT NAME	角法	版本
X ±0.35	X	±5°	审核	Gavin	菱形8PIN夹板母座		
X ±0.30	X	±2°	审核	郭治富			
XX ±0.20	XX	±1°	核准	黄国荣			
XXX ±0.10	XXX	±0.5°	核准				
			日期				
			2016-09-09				

