

目录 MAPX	设定内容 MODIFICATION	日期 DATE
------------	----------------------	------------

特性: Specifications:
电气: Electrical:

1. 接触阻抗: Contact Resistance:
30 milliohms MAX
2. 耐受电压: Dielectric With Standing Voltage:
500 V AC AT Sea Level
3. 绝缘阻抗: Insulation Resistance:
1000 MEGA ohms MIN

机构: Mechanical:







1. 结合力: Mating Force:
35 N MAX 最大 35 N
2. 拔出力: Unmating Force:
8 N MIN 最少 8 N

材料: Material:

1. 塑胶: PBT.
2. 端子: Contact: C2680
3. 外壳: Shell: C2680

电镀: Finish:

1. 端子: Contact: Plated Gold in Mating Area:
Tin/Lead On Solder Tails. 接触点镀金, 脚镀锡
 2. 外壳: Shell:
Nickel Plating . 镀镍
- 镀镍、镀金部分盐雾24H, 镀锡部分盐雾12H.



产品图
PRODUCT CHART DWG

深圳市精拓金电子有限公司

公差表 TOLERANCE UNLESS OTHERWISE		单位 UNITS	MM	制图 DRAWING	客户料号 PRODUCT PART NO.
X	±0.30	X'	±3	审核 CHND	产品名称 PRODUCT NM.
X	±0.25	X'	±3	核准 APPD	角法 VIB
XX	±0.20	XX'	±2	日期 DATE	版本 VER
未标注的公差按一般标准计算				2014/04/23	A0