

| | | |
|------|--------------|------|
| MAPX | MODIFICATION | DATE |
|------|--------------|------|

Specifications:


- Electrical:
- 1.Current Rating 1.5A/contact terminal
 - 2.Voltage Rating : 30V DC
 - 3.Contact Resistance: 30 milliohms MAX
 - 4.Dielectric Withstanding Voltage: 500 V AC AT Sea Level
 - 5.Insulation Resistance: 1000MEGA ohms MIN
- Mechanical:
- 1.Connector Mate and Unmate Force:
Mate force: 3.75kgf(MAX)
Unmate force: 0.40kgf(MIN)
 - 2.Terminal Retention : 0.40kgf(MIN)

Material:

- 1.Housing:
Hing Temperature Ternmaplastics,
UI 94V-0 LCP White/Black
- 2.Contact: Copper Alloy C2680
- 3.Shell: Copper Alloy C2680/SPCC

Finish:

- 1.Contact: Plated Gold in Mating Area; Tin On Solder Tails
- 2.Shell: Nickel Plating



深圳市精拓金电子有限公司

| | | | | | | | | | |
|--------------------------|-------|-------------------------------------|-------|-------------|------------|---------------|-----|-------------------------|------------------------|
| 产品图 PRODUCT CHART DWG | | 公差一览表 TOLERANCE UNLESS OTHERWISE | | 单位 UNITS | MM | 制图 DRAWING | 许榕强 | 制料号 PRODUCT PART NO. | MINI USB SPIN/F SMT 立贴 |
| X | ±0.15 | X | ±5° | 比例 SCALE | 1:1 | 审核 CHKD | 郭治富 | 产品名称 PRODUCT NO. | |
| X | ±0.10 | X | ±2° | 日期 DATE | 2016-09-09 | 核准 APPR | 黄国荣 | 角法 VIEW | |
| XX | ±0.05 | XX | ±1° | | | | | | 版本 VER |
| XXX | ±0.03 | XXX | ±0.5° | | | | | | AD |