



料号 material No.	品名 Parts Name	型号 Part NO.	接插规格 connecting spec	W	F	L	B	∅D	∅C	T
40-FDFNV1.25-250	全绝缘接头	FDFNV1.25-250	0.8*6.35	6.6	7.3	22.0	12.0	4.0	1.7	0.45



导线截面: 0.5-1.5mm<sup>2</sup> (美国线规22-16)  
 最大电流: I<sub>max</sub>=10A  
 材 质: 黄铜  
 绝缘套材料: 尼龙  
 颜色: 红色



DIMENSION		TOLERANCES		DWG. BY		CHK. BY		UNIT		mm		
0.0	±0.5											
0.00												
FIRST ANGLE PROJ				A	NEW PART	<i>wallian</i>	<i>zy.wang</i>	<i>202105</i>	APP. BY	<i>wang zhiyan</i>	DWG. NO.	HIMA/QR-JZ-40-FDFNV1.25-250
L.T.R.				REVISION RECORD	DWG. BY	CHK. BY	DATE	CHK. BY	APP. BY	<i>wang zhiyan</i>	DWG. NO.	HIMA/QR-JZ-40-FDFNV1.25-250

未经许可不得修改和复印  
 该知识产权属于技术质量部

**HIMA** 惠华  
 苏州惠华电子科技有限公司