



料号 material No.	品名 Parts Name	型号 Part NO.	接插规格 connecting spec	W	F	L	B	∅D	∅C	T
40-FDFNY5.5-250	全绝缘接头	FDFNY5.5-250	0.8*6.35	6.6	7.3	23.0	12.0	5.0	3.4	0.45



导线截面: 4-6mm² (美国线规12-10)
 最大电流: I_{max}=24A
 材 质: 黄铜
 绝缘套材料: 尼龙
 颜色: 黄色



未经许可不得修改和复印
 该知识产权属于技术质量部

DIMENSION		TOLERANCES		NEW PART		CHK. BY		DATE	
0.0		±0.5							
0.00									
FIRST ANGLE PROJ				A					
				LTR.	REVISION RECORD	DWG. BY	CHK. BY	DATE	
						<i>willian</i>	<i>zy. wang</i>	<i>202105</i>	
DWG. BY		<i>liu liang</i>		UNIT		mm			
CHK. BY		<i>willian</i>		REV.		A			
APP. BY		<i>wang zhiyan</i>		DWG. NO.		HIMA/QR-JZ-40-FDFNY5.5-250			

HIMA 惠华苏州惠华电子科技有限公司