


| | | | | |
|----------------|------------------|----------------|-----|---------|
| 料号 Part NO. | 品名 Parts Name | 型号 Part NO. | 端子数 | 长度 L |
| 41-PA007-3P | 端子台 | PA007-3P | 3 | 21.8 |



介绍:
剥线长度: 6.5mm (公厘) / 0.261in. (吋)
间距: 7.5mm
胶壳: 尼龙66工程塑料
线座: 铜合金, 镀锡; 方形接线孔
螺丝: 铁线, 镀锌; M3*5.35mm
弹片: 不锈钢

电流: 24A
电压: 400V
线径范围: 26-14AWG, Cu (UL), 0.5-1.5MM²

| DIMENSION | TOLERANCES | FIRST ANGLE PROJ | | |
|------------------|------------------------|---------------------|----------|-----------------|
| | | A | NEW PART | REVISION RECORD |
| 0.0 0.00 | ±0.5 | | | |
| | | | | |
| | | | | |
| | | | | |
| | | | | |
| DWG. BY | CHK. BY | APP. BY | UNIT | mm |
| <i>liu liang</i> | <i>sullivan</i> | <i>wang shiyuan</i> | REV. | A |
| DWG. NO. | HIWA/OR-JZ-41-PA007-3P | | | |



未经许可不得修改和复印
该知识产权属于技术质量部