

● ELECTRICAL PARAMETERS

谐振器产品技术指标	Min	Max	Units
1.Holder Type(型号规格)	#REF!		
2.Mode of Oscillation (振动模式)	FUND		
3. Frequency (标称频率)	24. 000000		MHz
4.Load Capacitance (CL) (负载电容)	12 ±10%		pF
5.Shunt Capacitance (Co) (静态电容)	0	7	pF
6. Equivalent Resistance (谐振电阻)		30	Ω
7.Frequency Tolerance at 25℃ (调整频差)	-10	10	ppm
8.Stability over operation temperance (温度频差)	± 30		ppm
9.Insulation Resistance (at DC 100V) (绝缘电阻)	500		MΩ
10.Drive Level (激励功率)	10		uw
11.Operating Temperature Range (工作温度范围)	-40	85	℃
12. Storage Temperature Range (储存温度范围)	-40	125	℃
13. Aging (老化率)	± 5		ppm/year
14. Other(其他)	DLD2<10 FDLD<10(0.01-100/STEP10)		

OUTLINE DIMENSIONS(UNIT:mm) 外形尺寸 (单位: mm)

