



Circuit Diagram

- NOTE:
1. Rating: AC125V 5A/250V 3A
  2. Operating force:  $25 \pm 10$ gf
  3. Mechanical Life: 1,000,000
  3. Electrical Life: 60000-10,000

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑧	Shrapnel 2	—	1	Copper Alloy	—	—
⑦	Shrapnel 1	—	1	Beryllium Copper	—	—
⑥	Contact	—	1	Copper Alloy	Plating silver	—
⑤	Lever	—	1	Copper Alloy	—	—
④	Terminal	—	3	Copper Alloy	Plating silver	—
③	Housing	—	1	PBT	Black	—
②	Knob	—	1	PBT	Black	—
①	Cover	—	1	PBT	Black	—

APPROVALS	DATE	TITLE:
DRAWN	JIANKUN.LIU	2015.5.26
CHECKED		
APPROVALS		

ELECTRONICS CO.,LTD	
MICRO SWITCHS	
PART NO.	K9-1910A

TOLERANCES ARE	30 <sup>±0.15</sup>	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROD.
	10 <sup>±0.20</sup>	±0.25				
	5 <sup>±0.10</sup>	±0.20	±2°	DRAWING NO.		SHEET 1 OF 1

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			