





## 微型保险丝(延时型)

### Micro Fuse (Time-Lag) 400V/300V/250V



**测试标准:**  
**Testing Standard:**  
 IEC60127-1 IEC60127-3 GB9364.1 GB9364.3

**额定分断能力:**  
**Interrupting Rating:**  
 35A or 10In Whichever is greater


**工作温度:**  
**Operating Temperature:**  
 -55°C ~ +125°C

**材料:**  
**Materials:**  
 Case:thermoplastic nylon  
 Base:thermoplastic nylon  
 Lead wire:tinned copper wire

**焊接方法:**  
**Soldering Method:**  
 Wave soldering: 260°C, 10s max  
 Manual soldering: 370°C, 5s max

Time-Current Characteristics

电流-时间曲线图



#### 电气特性: Electrical Characteristics

额定电流的% % of Ampere Rating	熔断时间 Opening Time (100mA~6.3A)	熔断时间 Opening Time (8A~10A)
210%	2 min Max(小于2分钟)	5 min Max(小于5分钟)
275%	400 ms~10 s	1 s~20 s
400%	150 ms~3 s	150 ms~3 s
1000%	20 ms~150 ms	20 ms~150 ms

目录编号: Catalog No.T:400V G:300V A:250V

目录编号 Catalog No.	额定电流 Ampere Rating	额定电压 Voltage Rating	最大电压降(mv) Max Voltage Drop	熔化热能 <sup>2</sup> Melting Integral (A <sup>2</sup> .S)	认证 Approvals							
					UL US	DVE	VDE	CQC	S	PS E JET	KC	
SMT0100T/G/A	100mA	400V/300V/250V	350	0.06	●							
SMT0125T/G/A	125mA	400V/300V/250V	300	0.08	●	○		○				
SMT0160T/G/A	160mA	400V/300V/250V	280	0.1	●	○		○				
SMT0200T/G/A	200mA	400V/300V/250V	260	0.2	●	○		○				
SMT0250T/G/A	250mA	400V/300V/250V	240	0.3	●	○		○				
SMT0400T/G/A	400mA	400V/300V/250V	200	0.5	●	○		○				
SMT0500T/G/A	500mA	400V/300V/250V	190	0.9	●	●		●	●		●	
SMT0630T/G/A	630mA	400V/300V/250V	180	1.2	●	●		●	●		●	
SMT0800T/G/A	800mA	400V/300V/250V	160	3.9	●	●		●	●		●	
SMT1100T/G/A	1A	400V/300V/250V	140	5.8	●	●		●	●	●	●	
SMT1125T/G/A	1.25A	400V/300V/250V	130	12.8	●	●		●	●	●	●	
SMT1160T/G/A	1.6A	400V/300V/250V	120	14.7	●	●		●	●	●	●	
SMT1200T/G/A	2A	400V/300V/250V	100	21.9	●	●		●	●	●	●	
SMT1250T/G/A	2.5A	400V/300V/250V	100	42.6	●	●		●	●	●	●	
SMT1315T/G/A	3.15A	400V/300V/250V	100	72	●	●		●	●	●	●	
SMT1400T/G/A	4A	400V/300V/250V	100	83.2	●	●		●	●	●	●	
SMT1500T/G/A	5A	400V/300V/250V	100	148	●	●	●	●	●	●	●	
SMT1630T/G/A	6.3A	400V/300V/250V	100	195	●	●	●	●	●	●	●	
SMT1800T/G/A	8A	400V/300V/250V	80	215	●		○	○				
SMT2100T/G/A	10A	400V/300V/250V	75	250	●		○	○				
SMT2120T/G/A	12A	400V/300V/250V	-	272	●							
SMT2150T/G/A	15A	400V/300V/250V	-	300	●							