

LQP03TN39NJ02#

indicates a package specification code.



< List of part numbers with package codes >
 LQP03TN39NJ02D , LQP03TN39NJ02J , LQP03TN39NJ02B

Shape



References

Packaging code	Specifications	Minimum quantity
D	φ180mm Paper taping	15000
J	φ330mm Paper taping	50000
B	Packing in bulk	500




Mass (Typ.)	
1 piece	0.0002g

Specifications

Inductance	39nH ±5%
Inductance test frequency	300MHz
Rated current (I _{temp}) (Based on Temperature rise)	120mA
Max. of DC resistance	3.00Ω
Q (min.)	9
Q test frequency	300MHz
Self resonance frequency (min.)	1500MHz
Operating temperature range (Self-temperature rise is not included)	-55~125°C
Series	LQP03TN_02

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



⚠ Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.