

SPECIFICATIONS


Current rating: 3A AC/DC
 Voltage rating: 250V AC/DC
 Contact resistance: 20mΩ max.
 Withstand voltage: 1000V AC/min
 Insulation resistance: 1000MΩ/min.
 Temperature range: -25°C~+85°C

Material:
 Part No: 2~20
 Housing: Nylon66, UL 94V-2

| Circuits | Part NO | Dimension (mm) | |
|----------|-----------|----------------|-------|
| | | A | B |
| 2 | 2510H-2P | 5.74 | 2.54 |
| 3 | 2510H-3P | 8.28 | 5.08 |
| 4 | 2510H-4P | 10.82 | 7.62 |
| 5 | 2510H-5P | 13.36 | 10.16 |
| 6 | 2510H-6P | 15.59 | 12.70 |
| 7 | 2510H-7P | 18.44 | 15.24 |
| 8 | 2510H-8P | 20.98 | 17.78 |
| 9 | 2510H-9P | 23.53 | 20.32 |
| 10 | 2510H-10P | 26.06 | 22.86 |
| 11 | 2510H-11P | 28.60 | 25.40 |
| 12 | 2510H-12P | 31.14 | 27.94 |
| 13 | 2510H-13P | 33.68 | 30.48 |
| 14 | 2510H-14P | 36.22 | 33.02 |
| 15 | 2510H-15P | 38.76 | 35.56 |
| 16 | 2510H-16P | 41.30 | 38.10 |
| 17 | 2510H-17P | 43.84 | 40.64 |
| 18 | 2510H-18P | 46.38 | 43.18 |
| 19 | 2510H-19P | 48.92 | 45.72 |
| 20 | 2510H-20P | 51.46 | 48.26 |

TOLERANCE TABLE

| | |
|------|-------|
| .0 | ±0.20 |
| .00 | ±0.10 |
| .000 | ±0.05 |

| | | | | | |
|------------------|------------------|--|-----------------|------|---|
| APPROVED: | DATE: |  深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD | | | |
| CHECKED: | DATE: | TITLE: 2510H-XP | | | |
| DRAWN: Jul i-Liu | DATE: 2008-04-07 | CLIENT P/N | / | | |
| | | UNIT | SCALE | REV. | |
| | | mm | free | ⊕ | A |
| | | FILE NO. | Ckmtw-2510-0001 | | |