


WAFER(90°)

Part No: 2510R
 Wafer: Nylon 66 UL94V-2
 Material: pin/post Brass tin plated
 Circuits: 2-20circuits available
 Insulation resistance: 1000M OHM/min
 Withstand voltage: 1000V AC/minute
 Current rating: 3A AC/DC
 Voltage rating: 250V AC
 Temperaturer range: -25°C to +85°C

Circuits	Part NO	Dimension(mm)	
		A	B
2	2510RF-2P	2.54	5.08
3	2510RF-3P	5.08	7.62
4	2510RF-4P	7.62	10.16
5	2510RF-5P	10.16	12.70
6	2510RF-6P	12.70	15.24
7	2510RF-7P	15.24	17.78
8	2510RF-8P	17.78	20.32
9	2510RF-9P	20.32	22.86
10	2510RF-10P	22.86	25.40
11	2510RF-11P	25.40	27.94
12	2510RF-12P	27.94	30.48
13	2510RF-13P	30.48	33.02
14	2510RF-14P	33.02	35.56
15	2510RF-15P	35.56	38.10
16	2510RF-16P	38.10	40.64
17	2510RF-17P	40.64	43.18
18	2510RF-18P	43.18	45.72
19	2510RF-19P	45.72	48.26
20	2510RF-20P	48.26	50.80

TOLERANCE TABLE	
.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	 深圳市灿科盟实业有限公司 Ckmtw CHANKLEMENT INDUSTRYCO., LTD			
CHECKED:	DATE:				
DRAWN:	DATE:	TITLE:			
L.Y.F	2008-04-07	2510RF-XP (贴片)			
UNIT	mm	SCALE	free	REV.	A
FILE NO.	Ckmtw-2510-0005				