


### SPECIFICATION

Voltage rating: AC, DC 250V  
 Current rating: AC, DC, 7A  
 Withstand voltage: 1500V AC min.  
 Insulation resistance: 1000MΩ min.  
 Temperature range: -25°C ~ +85°C  
 Applicable PC board thickness: 0.031" ~ 0.063"  
 (0.8 ~ 1.6mm)  
 Contact resistance: Initial value 10mΩ max.  
 After environmental testing 20mΩ max.


Material: Nylon66 UL94V-2  
 Contact: Brass  
 Finish: Tin-plated  
 Poles: 2-24  
 Color: Nature



P. C. B LAYOUT

### TOLERANCE TABLE

.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRY CO., LTD			
CHECKED:	DATE:	TITLE: 5557S-1*XP 空心针			
DRAWN:	DATE:	CLIENT P/N	/	SCALE	REV.
LXF	2008-04-11	UNIT	mm	free	⊕
		FILE NO.	Ckmtw-5557-0010		A