



P.C.B LAYOUT(Copper-side view)
10.80



DC MATE PLUG

Rating:0.5A 30V DC
Contact Resistance:100 mΩ Max.
Operating temperature:-20℃~70℃
Operating force:3-20N
Operating Life:5,000cycles

② Terminal	5	Phosphor bronze	Au Plating			
① Housing	1	Nylon	Black			
ITEM	PART NAME	TER.NO.	QTY.	MATERIAL	FINISHING	REMARK
APPROVALS		DATE				
DRAWN	J.X.Zhang	2013/11/11	ELECTRONICS CO.,LTD			
CHECKED			PHONE JACKES			
APPROVALS			PART NO.	DC-041		
TOLERANCES ARE		30~0.1±	±0.30	ANGLE	UNIT: mm	SCALE: 1:1
		10~0.30	±0.20			
		5~0.10	±0.15	±2°	DRAWING NO.	PROJ.
		~ 5	±0.10			SHEET 1 OF 1
ECN NO.	REV.	DATE.	DESCRIPTION.			
	A		NEW			