



CIRCUIT DIRGRAM



NOTE:
 Rating: DC 30V 0.1A
 Operating Force: 20±10gf
 Lifetime: 50,000 Cycles

PART NO.	H	H1	H2
K5-1628DA-01	8.8	8.2	6.8
K5-1628DA-02	7.9	7.5	6.1
K5-1628DA-03	8.4	7.7	7.1

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Spring	—	1	Beryllium copper	Ag Plated	—
④	Terminal	—	2	Phosphor Bronze	Ag Plated	—
③	Base	—	1	NYLON	Black	—
②	Cover	—	1	NYLON	Black	—
①	Slider	—	1	NYLON	Black	—

APPROVALS		DATE	TITLE:
DRAWN	J.X.Zhang	2013/9/23	DETECTOR SWITCHS
CHECKED			
APPROVALS			

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	TOLERANCES ARE	ANGLE	UNIT:	SCALE:	PROJ.	SHEET
	A		NEW				30~0.15	±2°	mm	1:1	PROJ.	1 OF 1
							10~0.30					
							5~1.0					
							~5					



ELECTRONICS CO.,LTD