



NOTE:
 Rating: DC 30V 0.1A
 Operating Force: 50±10gf
 Lifetime: 50,000 Cycles

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Spring	—	1	Beryllium copper	Ag Plated	—
④	Terminal	—	2	Phosphor Bronze	Ag Plated	—
③	Base	—	1	NYLON	Black	—
②	Cover	—	1	NYLON	Black	—
①	Slider	—	1	NYLON	Black	—

APPROVALS		DATE	TITLE:	
DRAWN	J.X.Zhang	2013/9/24	ELECTRONICS CO.,LTD	
CHECKED			DETECTOR SWITCHS	
APPROVALS			PART NO.	K5-1629DA-01

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	TOLERANCES ARE	ANGLE	UNIT:	SCALE:	DRAWING NO.	SHEET
	A		NEW				30~0.15 10~0.30 5~1.0	±0.30 ±0.20 ±0.15	mm	1:1		1 OF 1