

**技术参数 SPECIFICATIONS**


- 线数 (Poles) : 2~15(22)
- 适用线规 (Applicable wires) : AWG28#~22#
- 适应基板厚度 (Applicable PC board thickness) : 1.6mm
- 温度范围 (Temperature range) : -25℃~85℃
- 额定电压 (Voltage rating) : 250V.Ac/Dc
- 额定电流 (Current rating) : 3A
- 接触电阻 (Contact resistance) : ≤0.02Ω
- 绝缘电阻 (Insulation resistance) : ≥1000MΩ
- 耐压 (Withstand voltage) : 1000V.Ac/1min
- 材料 (Material) :  
 孔座 (Housing) : 尼龙 (PA66) UL94V-2(0)  
 针座 (Wafer) : 尼龙 (PA66) UL94V-2(0)  
 端子 (Terminal) : 磷青铜 (Phos.bronze Tin/plated)




**端子 TERMINAL (CH10)**

型号 Type	适用线规 Applicable wires mm	AWG#	电线外径 O.D of wire ins mm	数量 Quantity
HX25410-PT	0.08~0.33	28~22	1.0~1.8	6000PCS/包


**HX25410-PT (CH10)**




**HX25410-Y (CH10)**



**HX25411-A (S045)**



**HX25411-WA (S045)**



**安装尺寸 MOUNTING MEASUREMENT**



**孔座 HOUSING (CH10)**

线数 Poles	型号 Type	尺寸 Dimensions (mm)	A	B
2	HX25410-2Y	2.54	5.56	
3	HX25410-3Y	5.08	8.10	
4	HX25410-4Y	7.62	10.64	
4	HX25410-5Y	10.16	13.18	
6	HX25410-6Y	12.70	15.72	
7	HX25410-7Y	15.24	18.26	
8	HX25410-8Y	17.78	20.80	
9	HX25410-9Y	20.32	23.34	
10	HX25410-10Y	22.86	25.88	
11	HX25410-11Y	25.40	28.42	
12	HX25410-12Y	27.94	30.96	
13	HX25410-13Y	30.48	33.50	
14	HX25410-14Y	33.02	36.04	
15	HX25410-15Y	35.56	38.58	
...	...	...	...	...
22	HX25410-22Y	53.34	56.36	

**针座 WAFER (S045)**

线数 Poles	型号 Type 直式 (180°)	尺寸 Dimensions (mm)	A	B
2	HX25411-2A/WA	2.54	5.08	
3	HX25411-3A/WA	5.08	7.62	
4	HX25411-4A/WA	7.62	10.16	
5	HX25411-5A/WA	10.16	12.70	
6	HX25411-6A/WA	12.70	15.24	
7	HX25411-7A/WA	15.24	17.78	
8	HX25411-8A/WA	17.78	20.32	
9	HX25411-9A/WA	20.32	22.86	
10	HX25411-10A/WA	22.86	25.40	
11	HX25411-11A/WA	25.40	27.94	
12	HX25411-12A/WA	27.94	30.48	
13	HX25411-13A/WA	30.48	33.02	
14	HX25411-14A/WA	33.02	35.56	
15	HX25411-15A/WA	35.56	38.10	
...	...	...	...	...
22	HX25411-22A/WA	53.34	55.88	