



技术参数 SPECIFICATIONS

- 线数 (Poles) : 2~24
- 适用线规 (Applicable wires) : AWG30#~18#
- 适用基板厚度 (Applicable PC board thickness) : 1.6mm
- 温度范围 (Temperature range) : -25℃~85℃
- 额定电压 (Voltage rating) : 300V.Ac/Dc
- 额定电流 (Current rating) : 9A max
- 接触电阻 (Contact resistance) : $\leq 0.015\Omega$
- 绝缘电阻 (Insulation resistance) : $\geq 1000M\Omega$
- 耐压 (Withstand voltage) : 1500V.Ac/1min
- 材料 (Material) :
 - 孔座 (Housing) : 尼龙 (PA66) UL94V-2(0)
 - 针座 (Wafer) : 尼龙 (PA66) UL94V-2(0)
 - 端子 (Terminal) : 磷青铜 (Phos.bronze Tin/plated)


HX42003-WA (5569)




安装尺寸 MOUNTING MEASUREMENT




HX42003-WAG (5569)




安装尺寸 MOUNTING MEASUREMENT




HX42003-WAF (5569)



安装尺寸 MOUNTING MEASUREMENT



HX42003-WAK (5569)



双排管针座 WAFER(5569)

线数 Poles	型号 Type 号式 (90°)	尺寸 Dimensions (mm)		
		A	B	C
2	HX42003-2WA	0	5.4	15.2
4	HX42003-4WA	4.2	9.6	19.4
6	HX42003-6WA	8.4	13.8	23.6
8	HX42003-8WA	12.6	18.0	27.8
10	HX42003-10WA	16.8	22.2	32.0
12	HX42003-12WA	21.0	26.6	36.2

线数 Poles	型号 Type 号式 (90°)	尺寸 Dimensions (mm)		
		A	B	C
14	HX42003-14WA	25.2	30.6	40.4
16	HX42003-16WA	29.4	34.8	44.6
18	HX42003-18WA	33.6	39.0	48.8
20	HX42003-20WA	37.8	43.2	53.0
22	HX42003-22WA	42.0	47.4	57.2
24	HX42003-24WA	46.2	51.6	61.4